



ZEISS Cataract Wet Lab at APAO 2018

Date 8 - 10 February 2018 | 10:00 AM - 4:30 PM

Location Hong Kong Convention & Exhibition Centre – ZEISS Booth 3E-01

Perform every step of IOL implantation using the latest ZEISS technology in a wet lab setting. Visit ZEISS Booth 3E-01 to experience the latest ZEISS cataract solution.



ZEISS OPMI LUMERA® 700 and ZEISS CALLISTO eye® 3.6 iOCT

Experience markerless IOL alignment and integrated intraoperative OCT imaging – all in one device – from the ophthalmic microscope market leader.



ZEISS VISALIS® V500

In addition to premium cataract technologies, VISALIS V500 features high quality phaco and vitrectomy functions – eliminating the need for external modules and saving space.

To reserve a slot, please register via our local ZEISS representatives and indicate your preferred date and time. Learn more at www.zeiss.com/apao.

Not all products, services or offers are approved or offered in every market. Due to compliance regulations, we inform you that, if necessary, you must obtain your employer's permission and check local legislation regarding the content of the invitation. Also, due to compliance regulations, participation is limited to the invitee only.

